





















Roca

ATLAS







 P 	P bar	 MAX 10	
 P 	P bar	MIN 1  5 MAX	 3 2 
  T	°C	 80 MAX.	 65 50 
 Q (3 bar)	l/min	 8	 5 1,7 A5A3290C0D  20



A5A3090

A5A3190

A5A3290













A5A3090

A5A3190

A5A3290

A5A3090..M

A5A3290..M




A5A6090

A5A6190

3



A5A4290..T







4



A5A0190


A5A0290




A5A2A90

A5A2090

A5A2190



A5B4961TP0





5



A5A3390








A5A3990




A5A3390

A5A3990

A5A3790..M




A5A3D90




A5A3490



A5A3790

A5A3790..M







A5A2290






A5A0690










A5A2D90..T






A5252206




A5A3590



8




0%




100%




0%



100%



1	- AG0116100R		17	- A525004600		40	- AG0117300R	
2	- AG0085300R		18	- AG0116300R		41	- AG0119500R	
3	- A525023507		19	- AG0032300R		42	- AG0001907R	
4	- AG0141207R		20	- AG0110607R		43	- A525006500	
5	- AG0096307R		21	- AG0116400R		44	- AG0119600R	
6	- AG0096409R	D10X3/8"H L-420	22	- AG0116700R		45	- AG0142300R	
	- AG0096509R	D10x3/8"H L-600	23	- A525003600		46	- AG0142100R	
7	- AG0125909R	D10x1/2"F L-600	24	- AG0116500R		47	- AG0171400R	
	- AG0126009R	D10x1/2"F L-470	25	- AG0116600R		48	- AG0171500R	
8	- AG0163900R		26	- A525005200		49	- AG0171600R	
9	- AG0159300R		27	- AG0116800R		50	- AG0171700R	
10	- AG0046600R	(5 l/min)	28	- AG0103908R		51	- AG0171800R	
	- AG0129000R	(1,7 l/min)	29	- A5B1103..0		52	- AG0171900R	
11	- A525020600		30	- AG0003700R		53	- AG0172700R	
12	- A525004403	M8X85	31	- A525009800		54	- AG0172300R	
	- A525030303	M8X247	32	- A525005507		55	- AG0172200R	
13	- AG0075300R		33	- AG0036800R		56	- AG0123907R	
14	- AG0096200R		34	- AG0099007R		57	- AG0172800R	
15	- A525021200		35	- AG0033300R		58	- AG0172000R	
16	- AG0055800R		36	- AP00097500				
			37	- AG0117207R				
			38	- AG0117100R				
			39	- AG0117400R				



A523092507s



Roca Sanitario, S.A.
 Avda. Diagonal, 513
 08029 Barcelona
 SPAIN
 www.roca.com

933 LÍNEA DE ATENCIÓN
661 AL CONSUMIDOR
266 ESPAÑA

SERVICIO TÉCNICO
 ESPAÑA



productsupport.rs@roca.net
 soporteproducto.rs@roca.net